













**ACCESSORIES | LAMP OPTIONS**

LAMP	COMMENTS	WATTAGE	BEAM ANGLE	FOR USE WITH
 <b>Halogen MR-8</b>	2000 Average Life Hour	20	Wide	CG
		20N	Narrow	CG
 <b>Halogen MR-11</b>	2000 Average Life Hour	10	Wide	SM
		20	Wide	FC, MP, SM
		35	Wide	CL, TS
 <b>Halogen MR-16</b>	5000 Average Life Hour  10,000 Hour option available (for fixtures using 20/35/50 watt)	20	Wide	LO, LR, MU, RP, RS, TE
		20V	Very Narrow	LO, LR, MU, RP, RS, TE
		35	Wide	LO, LR, MU, RP, RS, TE
		50	Wide	LO, LR, MU, RP, TE
		35V	Very Narrow	LO, LR, MU, RP, RS, TE
		50N	Narrow	LO, LR, MU, RP, TE
		50V	Very Narrow	LO, LR, MU, RP, TE
 <b>Titan Halogen MR-16</b>	12,000 Average Life Hour (for fixtures using 20 watt)	20	Wide	LB
		35	Wide	LB
	18,000 Average Life Hour (for fixtures using 35/50 watt)	50	Wide	LB
 <b>Xenon G4</b>	10,000 Average Life Hour (for fixtures using 10/15 watt)	10	N/A	BD, CA, CB, CM, CP, CR, CV, DL, DM, DP, DR, DS, EA, GT, MM, PF, PR, PV, QF, SC, SP, RL, UN
	5000 Average Life Hour (for fixtures using 20 watt)	15	N/A	BD, CA, CB, CV, DL, DM, DR, DS, EA, PF, PR, QF, SC, SP
		20	N/A	BD, CA, CB, CM, CR, CV, DL, DM, DR, DS, EA, GN, GT, LM, PD, PF, PR, QF, RL, SC, SP
 <b>Halogen T3</b>	2000 Average Life Hour	5	N/A	SI
		10	N/A	BD, CA, CB, CR, CV, DL, DM, DP, DR, DS, EA, GT, MM, PF, PR, PV, QF, RL, SC, SI, SP,
		20	N/A	BD, CA, CB, CR, CV, DL, DM, DR, DS EA, GT, PF, PR, QF, RL, SC, SI, SP,
		35	N/A	GN, GT, RL, SI
 <b>Halogen AR-11</b>	2000 Average Life Hour	20	Wide	CL, ML, TC, TS, VL
		20N	Narrow	CL, PM, TC, TS, VL
		20V	Very Narrow	CL, TC, TS, VL
 <b>Halogen AR-20</b>	2000 Average Life Hour	50	Wide	TS
		50N	Narrow	TS
 <b>Incandescent 93</b>	900 Average Life Hour	12	N/A	AL, FG, LS, TD
 <b>Incandescent I141</b>	1200 Average Life Hour	18	N/A	AL, FG, TD
 <b>Incandescent I156</b>	1200 Average Life Hour	25	N/A	AL, FG, TD
 <b>Xenolux® PAR36</b>	8000 Average Life Hour	20	Wide	CF
		35	Wide	CF

**Beam Angle Key (approximate values)**

Very Narrow- 10° | Narrow- 25° | Wide- 40° | Very Wide- 60°